

COMPO S SOFTENING LENS

15710 0130



EXCLUSIVELY AVAILABLE IN INDIA



[Voir sur le site Web](#)



Informations générales

EMPLACEMENT	interieur-exterieur
FORME / TAILLE DE DÉCOUPE (MM)	circulaire - 26,5
POIDS (KG)	0.01
ORIENTATION	non réglable

Utilisation à quel endroit ?

9 15711 9210	COMPO S 92710
9 15711 9220	COMPO S 92720
9 15711 9230	COMPO S 92741
9 15711 9310	COMPO S 93010
9 15711 9320	COMPO S 93020
9 15711 9330	COMPO S 93041
9 15711 9410	COMPO S 94010
9 15711 9420	COMPO S 94020
9 15711 9430	COMPO S 94041
9 15712 9020	COMPO S SOFT 93020
9 15712 9030	COMPO S SOFT 93041
9 15713 9020	COMPO S TW 96520
9 15713 9030	COMPO S TW 96541
9 15714 9020	COMPO S TW 94020
9 15714 9030	COMPO S TW 94041
9 15719 9210	COMPO S HP 92710
9 15719 9220	COMPO S HP 92720
9 15719 9230	COMPO S HP 92741
9 15719 9310	COMPO S HP 93010
9 15719 9320	COMPO S HP 93020
9 15719 9330	COMPO S HP 93041
9 15719 9410	COMPO S HP 94010
9 15719 9420	COMPO S HP 94020
9 15719 9430	COMPO S HP 94041
9 15720 9020	COMPO S HP SOFT 93020
9 15720 9030	COMPO S HP SOFT 93041
9 15721 9020	COMPO S HP TW 96520
9 15721 9030	COMPO S HP TW 96541
9 15743 9220	COMPO S IP44 92720
9 15743 9230	COMPO S IP44 92741
9 15743 9320	COMPO S IP44 93020
9 15743 9330	COMPO S IP44 93041
9 15743 9420	COMPO S IP44 94020
9 15743 9430	COMPO S IP44 94041
9 15747 9220	COMPO S IP44 HP 92720
9 15747 9230	COMPO S IP44 HP 92741
9 15747 9320	COMPO S IP44 HP 93020
9 15747 9330	COMPO S IP44 HP 93041

DELTALIGHT

COMPO S SOFTENING LENS

15710 0130

9 15747 9420 COMPO S IP44 HP 94020

9 15747 9430 COMPO S IP44 HP 94041

Notes: