


SOFTENING LENS 75

REFERENCE19810 0150



 [View on website](#)



General info	
LOCATION	indoor
WEIGHT (KG)	0.1

For detailed installation instructions, please consult the manual : [19810_0150_HAND.pdf](#)

WHERE USED

19882 9211	SPY 90 ON 92718 DIM1
19882 9221	SPY 90 ON 92730 DIM1
19882 9231	SPY 90 ON 92745 DIM1
19882 9311	SPY 90 ON 93018 DIM1
19882 9321	SPY 90 ON 93030 DIM1
19882 9331	SPY 90 ON 93045 DIM1
19883 9210	SPY 90 92718 ADM
19883 9211	SPY 90 92718 ADM DIM1
19883 9215	SPY 90 92718 ADM DIM5
19883 9220	SPY 90 92730 ADM
19883 9221	SPY 90 92730 ADM DIM1
19883 9225	SPY 90 92730 ADM DIM5
19883 9230	SPY 90 92745 ADM
19883 9231	SPY 90 92745 ADM DIM1
19883 9235	SPY 90 92745 ADM DIM5
19883 9310	SPY 90 93018 ADM
19883 9311	SPY 90 93018 ADM DIM1
19883 9315	SPY 90 93018 ADM DIM5
19883 9320	SPY 90 93030 ADM
19883 9321	SPY 90 93030 ADM DIM1
19883 9325	SPY 90 93030 ADM DIM5
19883 9330	SPY 90 93045 ADM
19883 9331	SPY 90 93045 ADM DIM1
19883 9335	SPY 90 93045 ADM DIM5
19884 9015	SPY 90 TW 96518 ADM DIM5
19884 9025	SPY 90 TW 96530 ADM DIM5
19884 9035	SPY 90 TW 96545 ADM DIM5

Notes:

DELTALIGHT

SOFTENING LENS 75

19810 0150