




CABLE CLAMP

15229 0010 B

DISPONIBLE EN
NOIR 15229 0010 B



 [Voir sur le site Web](#)



Informations générales	
EMPLACEMENT	interieur
POIDS (KG)	0.1

Pour des instructions d'installation détaillées, veuillez consulter le manuel : [15229_0010_HAND.pdf](#)

Utilisation à quel endroit ?

279 773 811 921	MICROSPY 39 C 92745
279 773 811 931	MICROSPY 39 C 93045
308 23 03 83 ED8	SUPER-OH! XS 39 C DIM8
308 241 03 83 ED8	SUPER-OH! XS 39 C DIM8
472 121 811 921	HEDRA 391 C 92745
472 121 811 931	HEDRA 391 C 93045
472 122 811 921	HEDRA 392 C 92745
472 122 811 931	HEDRA 392 C 93045
472 123 811 921	HEDRA 393 C 92745
472 123 811 931	HEDRA 393 C 93045
472 221 01	HEDRA 451 C E27
472 221 922 ED8	HEDRA 451 C 92740 DIM8
472 221 932 ED8	HEDRA 451 C 93040 DIM8
472 222 01	HEDRA 452 C E27
472 222 922 ED8	HEDRA 452 C 92740 DIM8
472 222 932 ED8	HEDRA 452 C 93040 DIM8
472 321 00	HEDRA 621 C Hi
472 322 00	HEDRA 622 C Hi
25410 0000	MAGMA
28710 9208	TOUPE C AC 927 DIM8
28710 9308	TOUPE C AC 930 DIM8
28712 0000	TOUPE C E27
28811 9230	M - CUPPA C 92740 MDL
28811 9330	M - CUPPA C 93040 MDL
28812 9235	M - CUPPA C 92740 DIM5
28812 9335	M - CUPPA C 93040 DIM5
28813 9030	M - CUPPA C SOFT 93040 MDL
28814 9035	M - CUPPA C SOFT 93040 DIM5
28815 9230	CUPPA C 92740
28815 9330	CUPPA C 93040
28816 9030	CUPPA C SOFT 93040
100061 9208	TOUPE AC 927 ADM DIM8
100061 9308	TOUPE AC 930 ADM DIM8

DELTALIGHT

CABLE CLAMP

15229 0010 B

100062 9208	TOUPE AC 927 ADM1F DIM8
100062 9308	TOUPE AC 930 ADM1F DIM8
100063 0000	TOUPE E27 ADM
100064 0000	TOUPE E27 ADM1F

Notes: