




SHIFTLINE M26H + SBL 2m 930
DIM5

30411 9305 B

DISPONIBLE EN
NEGRO 30411 9305 B
BLANCO 30411 9305 W



 [Ver en el sitio web](#)



Información general	
UBICACIÓN	interior
INSTALACIÓN	Techo Al superficie,Techo Suspendido
PROTECCIÓN DE INGRESO	IP20
PESO (KG)	3.9
CAPACIDAD DE AJUSTE	no ajustable
INFORMACIÓN	LED line controllable via own DALI address
Información eléctrica	
ELÉCTRICO	48V-DC
CLASE	III
TIPO DE ATENUACIÓN	con DALI
CLASIFICACIÓN ENERGÉTICA	F
Información de la fuente de luz	
LIGHTSOURCE NAME	LED
FUENTE DE LUZ	LED FLEX 19W / CRI>90 / 3000K / 1905lm
INFORMACIÓN TÉCNICA LED (FUENTE DE LUZ)	1905lm // 19W // 100lm/W
Requisitos	
LED POWER SUPPLY 48V-DC SLM26 - C POWERBOX 48V-DC / 100W	
Opción	
SLM - CABLE SUSPENSION SINGLE 1,6m SLM - CURRENT SUPPLY SET 4 x 0,75mm² 1,6m BLACK DIM5 SLM - ROD SUSPENSION 0,8m + CONNECTION SLM - ROD SUSPENSION 0,8m	


Para obtener instrucciones de instalación detalladas, consulte el manual : [30411_XXX5_HAND.pdf](#)

SHIFTLINE M26H + SBL 2m 930 DIM5


30411 9305 B

PIEZAS COMPATIBLES

Accesorios de Fijación



23358 1510 SLM - ROD SUSPENSION 0,8m + CONNECTION




23358 1520 SLM - ROD SUSPENSION 0,8m




23359 0510 SLM - CABLE SUSPENSION SINGLE 1,6m

Cable de alimentación




23359 2240 SLM - CURRENT SUPPLY SET 4 x 0,75mm² 1,6m BLACK DIM5


Fuente de Alimentación LED




300 89 48 100 LED POWER SUPPLY 48V-DC / 100W DIN



300 89 48 240 LED POWER SUPPLY 48V-DC / 240W DIN



21012 0230 LED POWER SUPPLY 48V-DC / 100W




21012 0240 LED POWER SUPPLY 48V-DC / 200W

DELTALIGHT

SHIFTLINE M26H + SBL 2m 930 DIM5

30411 9305 B

Power box




23380 0060 SLM26 - C POWERBOX 48V-DC / 100W




LUMINARIAS COMPATIBLES

SHIFTLINE M26H - LED LINE OK




29320 9205 M26H - LED LINE OK 927 DIM5




29320 9305 M26H - LED LINE OK 930 DIM5

SPLITLINE M/SHIFTLINE M - CUPPA




28814 9035 M - CUPPA C SOFT 93040 DIM5


SPLITLINE M/SHIFTLINE M - DOT.COM M4




23355 9215 M - DOT.COM M4 92714 DIM5



23355 9225 M - DOT.COM M4 92732 DIM5



23355 9235 M - DOT.COM M4 92751 DIM5




23355 9315 M - DOT.COM M4 93014 DIM5


DELTALIGHT

SHIFTLINE M26H + SBL 2m 930 DIM5

30411 9305 B




23355 9325 M - DOT.COM M4 93032 DIM5




23355 9335 M - DOT.COM M4 93051 DIM5

SPLITLINE M/SHIFTLINE M - DOT.COM WALLWASH




23370 9205 M - DOT.COM WALLWASH 12 927 DIM5




23370 9305 M - DOT.COM WALLWASH 12 930 DIM5

SPLITLINE M/SHIFTLINE M - GIBBO




23354 9205 M - GIBBO 927 DIM5




23354 9305 M - GIBBO 930 DIM5

SPLITLINE M/SHIFTLINE M - HEDRA 39 C




22539 9235 M - HEDRA 39 C 92745 DIM5



22539 9335 M - HEDRA 39 C 93045 DIM5

SPLITLINE M/SHIFTLINE M - LED LINE




23350 0005 M - LED LINE HE 1 x 25,2W DIM5

DELTALIGHT


SHIFTLINE M26H + SBL 2m 930 DIM5

30411 9305 B

SPLITLINE M/SHIFTLINE M - MICROSPY 39 C




23353 9215 M - MICROSPY 39 C 92745 DIM5




23353 9315 M - MICROSPY 39 C 93045 DIM5


SPLITLINE M20/SHIFTLINE M26H - BOWIE




26719 9225 M20/M26H - BOWIE 2 92725 DIM5



26719 9235 M20/M26H - BOWIE 2 92737 DIM5




26719 9325 M20/M26H - BOWIE 2 93025 DIM5




26719 9335 M20/M26H - BOWIE 2 93037 DIM5


SPLITLINE M20/SHIFTLINE M26H - HALOSCAN HP



23144 9015 M20/M26H - HALOSCAN HP SOFT 93014 DIM5



23144 9025 M20/M26H - HALOSCAN HP SOFT 93021 DIM5






23144 9035 M20/M26H - HALOSCAN HP SOFT 93035 DIM5

DELTALIGHT


SHIFTLINE M26H + SBL 2m 930 DIM5

30411 9305 B



SPLITLINE M20/SHIFTLINE M26H - HALOSCAN MP




SPLITLINE M20/SHIFTLINE M26H - HEDRA



SPLITLINE M20/SHIFTLINE M26H - HEDRA L



SPLITLINE M20/SHIFTLINE M26H - JUM-OH! 2R



DELTALIGHT

SHIFTLINE M26H + SBL 2m 930 DIM5

30411 9305 B

SPLITLINE M20/SHIFTLINE M26H - JUM-OH! 4R




29418 9225 M20/M26H - JUM-OH! 4R 92730 DIM5




29418 9325 M20/M26H - JUM-OH! 4R 93030 DIM5

SPLITLINE M20/SHIFTLINE M26H - MULTINOVA 30




27955 9005 M20/M26H - MULTINOVA 30 SOFT 930 DIM5


SPLITLINE M20/SHIFTLINE M26H - NEEDLE




25017 9215 M20/M26H - NEEDLE 92713 DIM5



25017 9225 M20/M26H - NEEDLE 92733 DIM5




25017 9315 M20/M26H - NEEDLE 93013 DIM5




25017 9325 M20/M26H - NEEDLE 93033 DIM5

SPLITLINE M20/SHIFTLINE M26H - NEEDLE OK



25019 9215 M20/M26H - NEEDLE OK 92713 DIM5




25019 9225 M20/M26H - NEEDLE OK 92733 DIM5


DELTALIGHT

SHIFTLINE M26H + SBL 2m 930 DIM5

30411 9305 B




25019 9315 M20/M26H - NEEDLE OK 93013 DIM5




25019 9325 M20/M26H - NEEDLE OK 93033 DIM5


SPLITLINE M20/SHIFTLINE M26H - OBIN




30514 9225 M20/M26H - OBIN 92724 DIM5



30514 9235 M20/M26H - OBIN 92736 DIM5




30514 9325 M20/M26H - OBIN 93024 DIM5




30514 9335 M20/M26H - OBIN 93036 DIM5

SPLITLINE M20/SHIFTLINE M26H - OCTAV 27




29014 9225 M20/M26H - OCTAV 27 92730 DIM5



29014 9325 M20/M26H - OCTAV 27 93030 DIM5

SPLITLINE M20/SHIFTLINE M26H - OCTAV 39




29022 9225 M20/M26H - OCTAV 39 92720 DIM5


DELTALIGHT

SHIFTLINE M26H + SBL 2m 930 DIM5


30411 9305 B



29022 9235 M20/M26H - OCTAV 39 92740 DIM5




29022 9325 M20/M26H - OCTAV 39 93020 DIM5




29022 9335 M20/M26H - OCTAV 39 93040 DIM5

SPLITLINE M20/SHIFTLINE M26H - ODRON




26217 9205 M20/M26H - ODRON 1 92728/41 DIM5




26217 9305 M20/M26H - ODRON 1 93028/41 DIM5

SPLITLINE M20/SHIFTLINE M26H - ODRON 2




26219 9205 M20/M26H - ODRON 2 92728/41 DIM5




26219 9305 M20/M26H - ODRON 2 93028/41 DIM5

SPLITLINE M20/SHIFTLINE M26H - PION



26618 9225 M20/M26H - PION 92725 DIM5




26618 9235 M20/M26H - PION 92737 DIM5


DELTALIGHT

SHIFTLINE M26H + SBL 2m 930 DIM5

30411 9305 B



26618 9325 M20/M26H - PION 93025 DIM5



26618 9335 M20/M26H - PION 93037 DIM5

SPLITLINE M20/SHIFTLINE M26H - PUNK




23372 9215 M20/M26H - PUNK 39 92745 DIM5




23372 9315 M20/M26H - PUNK 39 93045 DIM5

SPLITLINE M20/SHIFTLINE M26H - SPY 27




23312 9225 M20/M26H - SPY 271 92730 DIM5




23312 9325 M20/M26H - SPY 271 93030 DIM5

SPLITLINE M20/SHIFTLINE M26H - SPY 27 2




23314 9225 M20/M26H - SPY 272 92730 DIM5



23314 9325 M20/M26H - SPY 272 93030 DIM5


SPLITLINE M20/SHIFTLINE M26H - SPY 27 2 L



23388 9225 M20/M26H - SPY 272 L 92730 DIM5


SHIFTLINE M26H + SBL 2m 930 DIM5

30411 9305 B




23388 9325 M20/M26H - SPY 272 L 93030 DIM5

SPLITLINE M20/SHIFTLINE M26H - SPY 27 L




23386 9225 M20/M26H - SPY 271 L 92730 DIM5




23386 9325 M20/M26H - SPY 271 L 93030 DIM5

SPLITLINE M20/SHIFTLINE M26H - SPY 39




23424 9025 M20/M26H - SPY 391 SOFT 93020 DIM5




23424 9035 M20/M26H - SPY 391 SOFT 93040 DIM5

SPLITLINE M20/SHIFTLINE M26H - SPY 39 2




23428 9025 M20/M26H - SPY 392 SOFT 93020 DIM5




23428 9035 M20/M26H - SPY 392 SOFT 93040 DIM5

SPLITLINE M20/SHIFTLINE M26H - SPY 39 FOCUS




23416 9205 M20/M26H - SPY 39 FOCUS 927 DIM5




23416 9305 M20/M26H - SPY 39 FOCUS 930 DIM5

SHIFTLINE M26H + SBL 2m 930 DIM5

SPLITLINE M20/SHIFTLINE M26H - SPY 39 FRAMER




23418 9305 M20/M26H - SPY 39 FRAMER 930 DIM5



Exploded view diagram of the front suspension assembly. The diagram shows the lower control arm (166), ball joint (16), and steering knuckle (142). The ball joint is shown inserted into the steering knuckle. The lower control arm is shown with a ball joint (16) attached to its end. The steering knuckle (142) is shown with a ball joint (16) attached to its end. The lower control arm (166) is shown with a ball joint (16) attached to its end. The steering knuckle (142) is shown with a ball joint (16) attached to its end. The lower control arm (166) is shown with a ball joint (16) attached to its end. The steering knuckle (142) is shown with a ball joint (16) attached to its end.



23426 9035 M20/M26H - SPY 391 L SOFT 93040 DIM5




166 16 46 92 139

0-85°/35°

23399 9035 M20/M26H - SPY 52 SOFT 93045 DIM5



SPLITLINE M20/SHIFTLINE M26H - SPY 52 FOCUS




Delta Light NV may revise the information and technical data at any time without notice. Version: 15/04/2026

DELTALIGHT

SHIFTLINE M26H + SBL 2m 930 DIM5


30411 9305 B

SPLITLINE M20/SHIFTLINE M26H - SPY 52 WALLWASH




19895 9005 M20/M26H - SPY 52 WALLWASH SOFT 930 DIM5


SPLITLINE M20/SHIFTLINE M26H - SPY 66



23360 9015 M20/M26H - SPY 66 TW 96518 DIM5




23360 9025 M20/M26H - SPY 66 TW 96530 DIM5




23360 9035 M20/M26H - SPY 66 TW 96545 DIM5

SPLITLINE M20/SHIFTLINE M26H - SPY 66 WALLWASH




24636 9205 M20/M26H - SPY 66 WALLWASH 927 DIM5




24636 9305 M20/M26H - SPY 66 WALLWASH 930 DIM5

SPLITLINE M20/SHIFTLINE M26H - SPY FOCUS




23379 9205 M20/M26H - SPY FOCUS LP 927 DIM5



23379 9305 M20/M26H - SPY FOCUS LP 930 DIM5

SPLITLINE M20/SHIFTLINE M26H - TWEETER




23351 9225 M20/M26H - TWEETER 92733 DIM5


DELTALIGHT

SHIFTLINE M26H + SBL 2m 930 DIM5


30411 9305 B



23351 9235 M20/M26H - TWEETER 92750 DIM5




23351 9325 M20/M26H - TWEETER 93033 DIM5




23351 9335 M20/M26H - TWEETER 93050 DIM5

SPLITLINE M20/SHIFTLINE M26H - TWEETER BL




23352 9205 M20/M26H - TWEETER BL 927 DIM5




23352 9305 M20/M26H - TWEETER BL 930 DIM5

SPLITLINE M20/SHIFTLINE M26H - VIZIR




23371 9215 M20/M26H - VIZIR 92708 DIM5




23371 9315 M20/M26H - VIZIR 93008 DIM5

SPY II 39 M CABLE



12306622MD00-90D2M4 SPY II 39 M CABLE SOFT CRI90 3000-1800K 26° MDL




12306622MD00-90D2S7 SPY II 39 M CABLE SOFT CRI90 3000-1800K 19° MDL


DELTALIGHT

SHIFTLINE M26H + SBL 2m 930 DIM5

30411 9305 B



12306622MD00-90D2V1 SPY II 39 M CABLE SOFT CRI90 3000-1800K 55° MDL



12306622MD00-90D2W1 SPY II 39 M CABLE SOFT CRI90 3000-1800K 35° MDL

Notes: