



SOFTENING LENS 72

201 05 04



Ø72



[Visualizza sul sito web](#)



Informazioni generali

AMBIENTE	indoor
PESO (KG)	0.1

Per istruzioni di installazione dettagliate, consultare il manuale : [201_05_04_HAND.pdf](#)

Dove usato

100047 9210	MINIGRID IN 1 HP 92720
100047 9220	MINIGRID IN 1 HP 92737
100047 9230	MINIGRID IN 1 HP 92750
100047 9310	MINIGRID IN 1 HP 93020
100047 9320	MINIGRID IN 1 HP 93037
100047 9330	MINIGRID IN 1 HP 93050
100048 9210	MINIGRID IN 2 HP 92720
100048 9220	MINIGRID IN 2 HP 92737
100048 9230	MINIGRID IN 2 HP 92750
100048 9310	MINIGRID IN 2 HP 93020
100048 9320	MINIGRID IN 2 HP 93037
100048 9330	MINIGRID IN 2 HP 93050
100049 9210	MINIGRID IN TRIMLESS 1 HP 92720
100049 9220	MINIGRID IN TRIMLESS 1 HP 92737
100049 9230	MINIGRID IN TRIMLESS 1 HP 92750
100049 9310	MINIGRID IN TRIMLESS 1 HP 93020
100049 9320	MINIGRID IN TRIMLESS 1 HP 93037
100049 9330	MINIGRID IN TRIMLESS 1 HP 93050
100050 9210	MINIGRID IN TRIMLESS 2 HP 92720
100050 9220	MINIGRID IN TRIMLESS 2 HP 92737
100050 9230	MINIGRID IN TRIMLESS 2 HP 92750
100050 9310	MINIGRID IN TRIMLESS 2 HP 93020
100050 9320	MINIGRID IN TRIMLESS 2 HP 93037
100050 9330	MINIGRID IN TRIMLESS 2 HP 93050

Notes:

DELTALIGHT

SOFTENING LENS 72

201 05 04